# Escape ESHG6031SKTF 60" x 31-38" x 22"

PRODUCT NUMBER: ESHG6031SKTF-LH & ESHG6031SKTF-RH

TECHNICAL SPECIFICATIONS		
Drain	End drain	
Pump Configuration: Select 1	Std. = Standard / Alt LF/RF Optional	
Bath Weight (empty)	140 lbs	
Gallons to Operate	33-51	
ELECTRICAL SPECIFICATIONS		
Motor/Pump	(1) 115v 20AMP GFCI Circuits	
Inline Stainless Steel Heater	(1) 115v 20AMP GFCI Circuit	

## STANDARD FEATURES & ACCESSORIES for HYDRO GOLD SERIES BATHS

## JETS

12 Water Massage Jets Back Massage System(s) (6 Jets) Accumassage Back and Neck Jets 6 Ultra Flow Jets -

## PUMPS

3.25 Hydropower 3-speed Pump Quiet Pad Anti-Vibration Mounted Pump

**HEATERS** Stainless Steel Electric Heater

## CONTROLS

Air Switch On/Off Control(s) For Hydro Pump & Mood Light 3 Speed Massage: High, Medium or Low

## PURITY

HydroClean Water Purity System HydroCleanse

## **HYDRO GOLD SERIES**



ATHERS: 1		Jet & Control
NSTALLATION		placement may vary
	DECK (D)	
	UNDER MOUNT (U)	
	ALCOVE (A)	
	FREESTANDING (F)	
	CLAWFOOT (L)	Curved Skirt
	PEDESTAL (P)	



## STANDARD ACCESSORIES

Mood Light Lift & Turn Drain - White, Biscuit, Bone, Brushed Nickel, Oil Rubbed Bronze, Polished Chrome **Deluxe Cushion Pillow** Integral Tile Flange EZ Level Adjustable Legs FDA Recipe Non-Toxic Food & Beverage Grade Plumbing (primarily) 30 Point Quality Assurance Factory Test

## REQUIREMENTS


Pump Locations: Select 1 Electrical: two 115v GFCI Circuits Drain: Select Color / Finish Tub should not be supported by the lip in any way.

Level tub & screw or glue adjustable legs to sub floor. **CUT OUT DIMENSIONS:** 

OVALS: A template will be provided RECTANGLES: Subtract 1" to 1.5" from length & width for hole cut out size

**EZ CLEAN CAST ACRYLIC** 

## **OPTIONAL FEATURES & ACCESSORIES** (Please type in the box below)



Some standard & most alternate pump locations may stickout past perimeter of the bath 1"-3". NOTE: Graphics may not be to scale. Specifications and features are subject to change without notice and are ± .25". All final measurements should be taken from tub on site. Access 18"x 18" or larger is required for each pump. Consult your contractor for installation requirements.