PRODUCT NUMBER: SEAG9440 ... D A

(1) 115v 20AMP GFCI Circuits

TECHNICAL SPECIFICATIONS	
Drain	End drain
Pump Location(s): Select 1	Std. = Standard / Alt LF/RF Optional
Bath Weight (empty)	215 lbs
Gallons to Operate	85-110
ELECTRICAL SPECIFICATIONS	

BATHERS: 1	
INSTALLATION	
•	DECK (D)
	UNDER MOUNT (U)
	ALCOVE (A)
	FREESTANDING (F)
	CLAWFOOT (L)
	PEDESTAL (P)

Jet & Control placement may vary

# STANDARD FEATURES & ACCESSORIES for AIR GOLD SERIES BATHS

Motor/Pump

18 EZ Clean™ Air Jets on Sidewall X

## **PUMPS**

1.25 Air Power Variable Speed, Pulse & Wave heated Air Pump Quiet Pad Anti-Vibration Mounted Pump

#### **HEATERS**

Warm Back Rest Tubing Zone

## **CONTROLS**

Air Switch On/Off Control(s) for mood lighting Variable Speed Air Massage Control Automatic Purge & Dry Cycle Control

#### **PURITY**

HydroCleanse

### STANDARD ACCESSORIES

Mood Light

Lift & Turn Drain - White, Biscuit, Bone, Brushed Nickel, Oil Rubbed Bronze, Polished Chrome

**Deluxe Cushion Pillow** 

EZ Level Adjustable Legs

FDA Recipe Non-Toxic Food & Beverage Grade Plumbing (primarily) 30 Point Quality Assurance Factory Test

Only Available in White

### **REQUIREMENTS**

Pump Locations: Select 1

Electrical: one 115v 20AMP GFCI Circuits

Drain: Select Color / Finish

Tub should not be supported by the lip in any way.

Level tub & screw or glue EZ Level adjustable legs to sub floor. **CUT OUT DIMENSIONS:** 

OVALS: A template will be provided


**RECTANGLES:** Subtract 1" to 1.5" from length & width for hole


**EZ CLEAN CAST ACRYLIC** LIMITED LIFETIME WARRANTY (VL) us ANSI



## **OPTIONAL FEATURES & ACCESSORIES** (Please type in the box below)

- A X HTT® Leg Therapy Air Massage System includes 10 Air Jets on the floor. Optional on Combo Plat and Combo Gold Series
- **B** X 6 Jet HTT® Back Massage System: N/A on Combo Series-Standard on Plat series
- **ⓒ SWarm Back Tubing Zone**





Some standard & most alternate pump locations may stickout past perimeter of the bath 1"-3". NOTE: Graphics may not be to scale. Specifications and features are subject to change without notice and are ± .25". All final measurements should be taken from tub on site.

Access 18"x 18" or larger is required for each pump. Consult your contractor for installation requirements.