#### Zen ZECS6030SKTF 60" x 30" x 23"

PRODUCT NUMBER: ZECS6030SKTF-LH & ZECS6030SKTF-RH



# **COMBINATION SILVER SERIES**



TECHNICAL SPECIFICATIONS		
Drain	End drain	
Pump Location(s): Select 2	Std. = Standard / Alt LF/RF Optional	
Bath Weight (empty)	160 lbs	
Gallons to Operate	38-56	

ELECTRICAL SPECIFICATIONS	
Motor/Pump	(2) 115v 20AMP GFCI Circuits
Inline Stainless Steel Heater	(Opt.) 115v 20AMP GFCI Circuit

BATHERS: 1		
INSTALLATION		
	DECK (D)	
	UNDER MOUNT (U)	
·	ALCOVE (A)	
	FREESTANDING (F)	
	CLAWFOOT (L)	
	PEDESTAL (P)	





# STANDARD FEATURES & ACCESSORIES for COMBINATION SILVER SERIES BATHS

21 Air & Water Massage Jets Accumassage Back, Neck Jets Ultra Flow Jets - ( )-

Micro Flow Jets (•)

# Classic Air Jets O

**PUMPS** 

2.25 Hydropower 1-speed Pump 1.0 Air Power 3-Speed Warm Air Pump Quiet Pad Anti-Vibration Mounted Pump

### **CONTROLS**

Air Switch On/Off Control(s) Automatic Purge & Dry Cycle Control

#### **PURITY**

HydroClean Water Purity System HydroCleanse

## STANDARD ACCESSORIES

Mood Light

Lift & Turn Drain - White, Biscuit, Bone, Brushed Nickel, Oil Rubbed Bronze, Polished Chrome

**Deluxe Cushion Pillow** 

Integral Skirt with Magnetic Access Panel

EZ Level Adjustable Legs

FDA Recipe Non-Toxic Food & Beverage Grade

Plumbing (primarily)

30 Point Quality Assurance Factory Test

# **REQUIREMENTS**

Pump Locations: Select 2

Electrical: two 115v 20amp GFCI Circuits

Tub should not be supported by the lip in any way. Leve tub & screw or glue adjustable legs to sub floor.

**CUT OUT DIMENSIONS:** 

**OVALS:** A template will be provided

RECTANGLES: Subtract 1" to 1.5" from length & width for hole


cut out size

**EZ CLEAN CAST ACRYLIC** LIMITED LIFETIME WARRANTY



# **OPTIONAL FEATURES & ACCESSORIES**

(Please type in the box below)



Some standard & most alternate pump locations may stickout past perimeter of the bath 1"-3". NOTE: Graphics may not be to scale. Specifications and features are subject to change without notice and are ± .25". All final measurements should be taken from tub on site.

Access 18"x 18" or larger is required for each pump. Consult your contractor for installation requirements.