Zen ZECS6642SD

66" x 42" x 23"

PRODUCT NUMBER: ZECS6642SD ... D 0 A

COMBINATION SILVER SERIES

TECHNICAL SPECIFICATIONS	
Drain	Side drain
Pump Location(s): Select 2	Std. = Standard / Alt LF/RF Optional
Bath Weight (empty)	180 lbs
Gallons to Operate	57-83
ELECTRICAL SPECIFICATIONS	
Motor/Pump	(2) 115v 20AMP GFCI Circuits

BATHERS: 2	
INSTALLATION	
•	DECK (D)
$\lceil \cdot \rceil$	UNDER MOUNT (U)
•	ALCOVE (A)
	FREESTANDING (F)
	CLAWFOOT (L)
	PEDESTAL (P)

Jet & Control placement may vary

STANDARD FEATURES & ACCESSORIES for COMBINATION SILVER SERIES BATHS _

(Opt.) 115v 20AMP GFCI Circuit

JETS

21 Air & Water Massage Jets Accumassage Back, Neck Jets Ultra Flow Jets 👈

Inline Stainless Steel Heater

Micro Flow Jets (•) Classic Air Jets

PUMPS

2.25 Hydropower 1-speed Pump 1.0 Air Power 3-Speed Warm Air Pump Quiet Pad Anti-Vibration Mounted Pump

CONTROLS

Air Switch On/Off Control(s) Automatic Purge & Dry Cycle Control

PURITY

HydroClean Water Purity System HydroCleanse

STANDARD ACCESSORIES

Mood Light

Lift & Turn Drain - White, Biscuit, Bone, Brushed Nickel, Oil Rubbed Bronze, Polished Chrome

Deluxe Cushion Pillow

EZ Level Adjustable Legs FDA Recipe Non-Toxic Food & Beverage Grade

Plumbing (primarily)

30 Point Quality Assurance Factory Test

REQUIREMENTS

Pump Location(s): Select 2

Electrical: two 115v 20AMP GFCI Circuits

Tub should not be supported by the lip in any way. Level tub & screw or glue EZ Level adjustable legs to sub floor. **CUT OUT DIMENSIONS:**

OVALS: A template will be provided

RECTANGLES: Subtract 1" to 1.5" from length & width for hole


cut out size

EZ CLEAN CAST ACRYLIC LIMITED LIFETIME WARRANTY (UL) US ANSI




OPTIONAL FEATURES & ACCESSORIES


(Please type in the box below)



Bath includes EZ Level Legs **INSTALLATION WILL NOT REQUIRE MORTAR BEDDING**







Some standard & most alternate pump locations may stickout past perimeter of the bath 1"-3". NOTE: Graphics may not be to scale. Specifications and features are subject to change without notice and are ± .25". All final measurements should be taken from tub on site.

Access 18"x 18" or larger is required for each pump. Consult your contractor for installation requirements.