# Zen ZEHS7232SD 72" x 32" x 23"

PRODUCT NUMBER: ZEHS7232SD

# HYDRO SILVER SERIES

Jet &

Control placement

may vary

Health ... Our F

| TECHNICAL SPECIFICATIONS      |                                      |
|-------------------------------|--------------------------------------|
| Drain                         | Side drain                           |
| Pump Location(s): Select 1    | Std. = Standard / Alt LF/RF Optional |
| Bath Weight (empty)           | 185 lbs                              |
| Gallons to Operate            | 67-85                                |
| ELECTRICAL SPECIFICATIONS     |                                      |
| Motor/Pump                    | (1) 115v 20AMP GFCI Circuits         |
| Inline Stainless Steel Heater | (Opt) 115v 20AMP GFCI Circuit        |

### STANDARD FEATURES & ACCESSORIES for HYDRO SILVER SERIES BATHS

#### JETS

9 Water Jets Tri-Zone Back Systems 3 Jets Ultra Flow Jets -Micro Flow Jets (•)

#### PUMPS

2.25 Hydropower 1-speed Pump Quiet Pad Anti-Vibration Mounted Pump

CONTROLS Air Switch On/Off Control(s)

#### PURITY

HydroClean Water Purity System HydroCleanse

#### STANDARD ACCESSORIES

FDA Recipe Non-Toxic Food & Beverage Grade Plumbing (primarily) 30 Point Quality Assurance Factory Test EZ Level Adjustable Legs

## REQUIREMENTS

**BATHERS: 2** 

•

.

INSTALLATION

DECK (D)

ALCOVE (A) FREESTANDING (F) CLAWFOOT (L) PEDESTAL (P)


UNDER MOUNT (U)

Pump Locations: Select 1 Electrical: one 115v 20AMP GFCI Circuits Tub should not be supported by the lip in any way. Level tub & screw or glue EZ Level adjustable legs to sub floor. **CUT OUT DIMENSIONS:** OVALS: A template will be provided RECTANGLES: Subtract 1" to 1.5" from length & width for hole cut out size

**EZ CLEAN CAST ACRYLIC** LIMITED LIFETIME WARRANTY



#### **OPTIONAL FEATURES & ACCESSORIES** (Please type in the box below)



Some standard & most alternate pump locations may stickout past perimeter of the bath 1"-3". NOTE: Graphics may not be to scale. Specifications and features are subject to change without notice and are ± .25". All final measurements should be taken from tub on site. Access 18"x 18" or larger is required for each pump. Consult your contractor for installation requirements.