PRODUCT NUMBER: ZEHP7242 . D U A

**HYDRO PLATINUM SERIES** 

TECHNICAL SPECIFICATIONS	
Drain	End drain
Pump Location(s): Select 2	Std. = Standard / Alt LF/RF Optional
Bath Weight (empty)	190 lbs
Gallons to Operate	83-108
ELECTRICAL SPECIFICATIONS	
Motor/Pump	(2) 115v 20AMP GFCI Circuits

BATHERS: 1	
IN:	STALLATION
oxdot	DECK (D)
•	UNDER MOUNT (U)
•	ALCOVE (A)
	FREESTANDING (F)
	CLAWFOOT (L)
	PEDESTAL (P)
	PEDESTAL (P)



# STANDARD FEATURES & ACCESSORIES for HYDRO PLATINUM SERIES BATHS \_

(1) 115v 20AMP GFCI Circuit

### **JETS**

15 Water Jets Back Massage System(s) (7 Jets) Neck Massage Pillow (2 Jets) (⊕⊕) Sole Soother Jet(s) Accumassage Back, Neck Ultra Flow Jets - -

Inline Stainless Steel Heater

# **PUMPS**

Two 2.25 Hydropower 3-speed Pumps (End Drain Tubs) Quiet Pad Anti-Vibration Mounted Pump

#### **HFATERS**

Stainless Steel Electric Heater

# **CONTROLS**

Air Switch On/Off Control(s) For Chromatherapy Lighting 3 Speed Massage: High, Medium or Low

### **PURITY**

HydroClean Water Purity System HydroCleanse

# STANDARD ACCESSORIES

Grab Bar(s) - 2 on End Drain baths - White, Biscuit, Bone, Brushed Nickel, Polished Chrome

Chromatherapy Lighting

Deluxe Cable Drain - White, Biscuit, Bone, Brushed Nickel,

Oil Rubbed Bronze, Polished Chrome

Deluxe Cushion Pillow on two person baths

Neck Massage Pillow

EZ Level Base

FDA Recipe Non-Toxic Food & Beverage Grade Plumbing (primarily) 30 Point Quality Assurance Factory Test

## **REQUIREMENTS**

Pump Locations: Select 2

Electrical: three 115v 20AMP GFCI Circuits Drain and Grab Bars: Select Color / Finish

Tub should not be supported by the lip in any way.

Level tub & screw or glue EZ Level adjustable legs to sub floor. **CUT OUT DIMENSIONS:** 

**OVALS:** A template will be provided


**RECTANGLES:** Subtract 1" to 1.5" from length & width for hole cut out size

EZ CLEAN CAST ACRYLIC
LIMITED LIFETIME WARRANTY

© UL) US ANSI

# **OPTIONAL FEATURES & ACCESSORIES**

(Please type in the box below)



Some standard & most alternate pump locations may stickout past perimeter of the bath 1"-3". NOTE: Graphics may not be to scale. Specifications and features are subject to change without notice and are ± .25". All final measurements should be taken from tub on site. Access 18"x 18" or larger is required for each pump. Consult your contractor for installation requirements.