Zen Oval ZOHP6642 66" x 42" x 24"

PRODUCT NUMBER: ZOHP6642

TECHNICAL SPECIFICATIONS		E
Drain	End drain	I
Pump Location(s): Select 2	Std. = Standard / Alt LF/RF Optional	•
Bath Weight (empty)	160 lbs	•
Gallons to Operate	76-88	
ELECTRICAL SPECIFICATIO	NS	
Motor/Pump	(2) 115v 20AMP GFCI Circuits	
Inline Stainless Steel Heater	(1) 115v 20AMP GFCI Circuit	

STANDARD FEATURES & ACCESSORIES for HYDRO PLATINUM SERIES BATHS

JETS

15 Water Jets Back Massage System(s) (7 Jets) Neck Massage Pillow (2 Jets) $(\oplus \oplus)$ Sole Soother Jet(s) 🛞 Accumassage Back, Neck Ultra Flow Jets -

PUMPS

Two 2.25 Hydropower 3-speed Pumps (End Drain Tubs) Quiet Pad Anti-Vibration Mounted Pump

HEATERS

Stainless Steel Electric Heater

CONTROLS


Air Switch On/Off Control(s) For Chromatherapy Lighting Air Switch On/Off with digital Temperature Readout Control 3 Speed Massage: High, Medium or Low

PURITY

HydroClean Water Purity System HydroCleanse

OPTIONAL FEATURES & ACCESSORIES (Please type in the box below)

HYDRO PLATINUM SERIES







STANDARD ACCESSORIES


Grab Bar(s) - 2 on End Drain baths - White, Biscuit, Bone,
Brushed Nickel, Polished Chrome
Chromatherapy Lighting
Deluxe Cable Drain - White, Biscuit, Bone, Brushed Nickel,
Oil Rubbed Bronze, Polished Chrome
Deluxe Cushion Pillow on two person baths
Neck Massage Pillow
EZ Level Base
FDA Recipe Non-Toxic Food & Beverage Grade Plumbing (primarily)
30 Point Quality Assurance Factory Test

Jet &

REQUIREMENTS

Pump Locations: Select 2 Electrical: three 115v 20AMP GFCI Circuits Drain and Grab Bars: Select Color / Finish Tub should not be supported by the lip in any way. Level tub & screw or glue EZ Level adjustable legs to sub floor. CUT OUT DIMENSIONS: OVALS: A template will be provided **RECTANGLES:** Subtract 1" to 1.5" from length & width for hole cut out size

EZ CLEAN CAST ACRYLIC



Some standard & most alternate pump locations may stickout past perimeter of the bath 1"-3". NOTE: Graphics may not be to scale. Specifications and features are subject to change without notice and are ± .25". All final measurements should be taken from tub on site. Access 18"x 18" or larger is required for each pump. Consult your contractor for installation requirements.